

HUBBELL

Power Systems

Terminal, Compression

By ANDERSON
Catalog # [VACL2012BN](#)



VERSAtile Aluminum Compression Terminal, 2/0 str AL/CU, 2 H, 1/2"

Features

Rated at 34.5 KV. UL listed for aluminum or copper conductors. CSA certified.

General

Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
Die Size	*See Resources / Downloads for die selection and installation instructions
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy - Tin Plated
Material - Body	Aluminum
Number of Pad Holes	2
Physical Attribute - Number of Holes	2
Style	Pressed Tubing
UPC	096359334057

Dimensions

Diameter - Pad Bolt	0.5 in
Dimension - Bolt Hole Size inch	0.500 in
Weight	0.098 lb

Conductor Related

Conductor Compatibility	ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18
Conductor Diameter (VersaCrimp) - Maximum	0.419 in
Conductor Diameter (VersaCrimp) - Minimum	0.232 in

Certifications And Compliance

UL Listed	Yes
-----------	-----

Logistics

Carton Quantity	108
-----------------	-----

Product Assets

[Catalogs - Distribution Connectors](#)
[Installation Manuals - VACL Terminal Die Chart](#)
[Sales Drawings - VACL Terminal Sales Drawing](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-VACL2012BN-SPEC-EN | REV 6/2024