

Terminal, Compression

By ANDERSON
Catalog # [VACL25012](#)

VERSAtile Aluminum Compression Terminal, 250MCM AL/CU, 1 H, 1/2"



*Representative Image

Features

- Rated at 34.5 KV. UL listed for aluminum or copper conductors. CSA certified.

General

Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
Die Size	*See Resources / Downloads for die selection and installation instructions
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy - Tin Plated
Material - Body	Aluminum
Number of Pad Holes	1
Physical Attribute - Number of Holes	1
Style	Pressed Tubing
UPC	096359334095

Dimensions

Diameter - Pad Bolt	0.5 in
Dimension - Bolt Hole Size inch	0.500 in
Weight	0.245 lb

Conductor Related

Conductor Compatibility	ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;ACSR-Pigeon-3/0-6/1;ACSR-Penguin-4/0-6/1;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAC-Valerian-250-19;AAAC 6201 Alloy-Azusa-123.3-6/18;AAAC 6201 Alloy-Anaheim-155.4-6/18;AAAC 6201 Alloy-Amherst-195.7-6/18;AAAC 6201 Alloy-Alliance-246.9-6/18
Conductor Diameter (VersaCrimp) - Maximum	0.575 in
Conductor Diameter (VersaCrimp) - Minimum	0.368 in

Certifications and Compliance

UL Listed	Yes
-----------	-----

Logistics

Carton Quantity	100
-----------------	-----

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Installation Manuals - VACL Terminal Die Chart](#)
[Sales Drawings - VACL Terminal Sales Drawing](#)