

HUBBELL Power Systems

Turnbuckle

By ANDERSON

Catalog # [TB58EE6LN](#)

Turnbuckles are used as adjustable extension links to maintain proper tower clearance on assemblies at tower end. Jaw ends are supplied with bolt, nut, and humpback cotter pin. Add "LN" suffix if jam nuts are required. Remove "BNK" suffix for type EE turnbuckles.



Features

- "Turnbuckle, 5/8", Eye-Eye, Forged Steel, Diameter = .63", Take Up = 6.00" and Ult. Strength = 17,500 LBS
- The torque required to rotate the boss of a turnbuckle under tension can be calculated by the formula:
- $T = 2 (kdW/12) \text{ ft-lb}$
- Where: k = Friction factor (0.16)
- d = Nominal thread diameter (inches)
- W = Applied tension load (lb)
- Example: 3/4" turnbuckle under 4,000 lb tension
- $T = 2(0.16 \times .63 \times 4000 / 12) = 67 \text{ ft-lb}$

General

Material	Steel
Number of Bolt Holes	0
Series	TYPE EE
Strength Rating - Ultimate	17500 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359805502

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Take Up	6 in
Weight	0.98 lb

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-TB58EE6LN-SPEC-EN | REV 6/2024