

## Terminal, Compression

By ANDERSON  
Catalog # [VACL4012](#)



VERSAtile Aluminum Compression Terminal

\*Representative Image

### Features

- Rated at 34.5 KV. UL listed for aluminum or copper conductors. CSA certified.

### General

Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
Die Size	*See Resources / Downloads for die selection and installation instructions
Material	Aluminum Alloy - Tin Plated
Material - Body	Aluminum
Number of Pad Holes	1
Physical Attribute - Number of Holes	1
Style	Pressed Tubing
UPC	096359365341

### Dimensions

Diameter - Pad Bolt	0.5 in
Dimension - Bolt Hole Size inch	0.500 in
Weight	0.225 lb

### Conductor Related

Conductor Compatibility	ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;ACSR-Pigeon-3/0-6/1;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18;AAAC 6201 Alloy-Anaheim-155.4-6/18;AAAC 6201 Alloy-Amherst-195.7-6/18
Conductor Diameter (VersaCrimp) - Maximum	0.528 in
Conductor Diameter (VersaCrimp) - Minimum	0.292 in

### Certifications and Compliance

UL Listed	Yes
-----------	-----

### Logistics

Carton Quantity	144
-----------------	-----

### Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)  
[Installation Manuals - VACL Terminal Die Chart](#)  
[Sales Drawings - VACL Terminal Sales Drawing](#)