

Terminal, Compression

By ANDERSON
Catalog # [VACL4038](#)

VERSAtile Aluminum Compression Terminal, 4/0 str AL/CU, 1 H, 3/8"



*Representative Image

Features

- Rated at 34.5 KV. UL listed for aluminum or copper conductors. CSA certified.

General

Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
Die Size	*See Resources / Downloads for die selection and installation instructions
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy - Tin Plated
Material - Body	Aluminum
Number of Pad Holes	1
Physical Attribute - Number of Holes	1
Style	Pressed Tubing
UPC	096359334200

Dimensions

Diameter - Pad Bolt	0.38 in
Dimension - Bolt Hole Size inch	0.380 in
Weight	0.098 lb

Conductor Related

Conductor Compatibility	ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;ACSR-Pigeon-3/0-6/1;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18;AAAC 6201 Alloy-Anaheim-155.4-6/18;AAAC 6201 Alloy-Amherst-195.7-6/18
Conductor Diameter (VersaCrimp) - Maximum	0.528 in
Conductor Diameter (VersaCrimp) - Minimum	0.292 in

Certifications and Compliance

UL Listed	Yes
-----------	-----

Logistics

Carton Quantity	48
-----------------	----

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Installation Manuals - VACL Terminal Die Chart](#)
[Sales Drawings - VACL Terminal Sales Drawing](#)