

**Aluminum Compression Terminal
for #4 AL/CU, #2 sol CU, #4 6/1,
7/1 ACSR, #2 COMPACT**

By ANDERSON
Catalog # [VAUL412](#)

Aluminum Compression Terminal for #4 AL/CU, #2 sol CU, #4 6/1, 7/1 ACSR, #2 COMPACT, 1 HOLE, Meets ANSI C119.4 Class C performance on copper conductor



*Representative Image

Features

- Connectors are prefilled with rubber compatible inhibitor and sealed with color coded end caps.

General

Color Code	Orange
Crimp Method	VERSAtile™ (Accomodates Conventional And Anderson Tools)
Die Index	5/8 (243, BG)
Die Size	*See Resources / Downloads for die selection and installation instructions
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum
Material - Body	Aluminum
Number of Pad Holes	1
Physical Attribute - Number of Holes	1
Plating	No
Style	Impact Extruded
UPC	096359334903

Dimensions

Diameter - Pad Bolt	0.5 in
Dimension - Hole Size inch	0.500 in
Weight	0.098 lb

Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;AAC-Peachbell-6-7;AAC-Rose-4-7;AAC-Iris-2-7;AAAC 6201 Alloy-Akron-30.58-6/18;AAAC 6201 Alloy-Alton-48.69-6/18
Conductor Diameter (VersaCrimp) - Maximum	0.268 in
Conductor Diameter (VersaCrimp) - Minimum	0.146 in

Certifications and Compliance

UL Listed	No
-----------	----

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Installation Manuals - VAUL Terminals Installation Procedures](#)
[Sales Drawings - VAULxxx_drawing](#)

