


HUBBELL Power Systems

Compression Splice VERSAtile™ Minimum Tension

By ANDERSON
Catalog # [VAUS14](#)

Aluminum, Minimum tension, Reducing splice for #2 - #1* CU,
AAC, ACSR.



*Representative Image

Features

- See product drawing for complete reducing range
- Entire VAUS series installs with only 4 common die sizes
- Color coded end caps for quick conductor sizing through 4/0

General

Catalog Number	VAUS14
Color Code	Red; Orange
Compression Method	VersaCrimp or Conventional
Die Tooling	Die Tooling
Cover Available	No
Die Size	*See Resources / Downloads for die selection and installation instructions
EU RoHS Indicator	Contact Manufacturer
End A Type	#2 - #1 str AL/CU, #2 ACSR
End B Type	#4 str - #2 sol AL/CU, #4 ACSR
Material	Aluminum Alloy
UPC	096359335139

Dimensions

Length Before Compression	2 in
---------------------------	------

Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;AAC-Peachbell-6-7;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAAC 6201 Alloy-Akron-30.58-6/18;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18
Conductor Diameter (Conventional Tooling) End A - Maximum	0.281 in
Conductor Diameter (Conventional Tooling) End A - Minimum	0.355 in
Conductor Diameter (Conventional Tooling) End B - Maximum	0.281 in
Conductor Diameter (Conventional Tooling) End B - Minimum	0.355 in

Product Assets

[Catalogs - Distribution Connectors](#)

[Sales Drawings - Aluminum_Compression_Sleeve\(CC-11615\)](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-VAUS14-SPEC-EN | REV 6/2024