

HUBBELL

Power Systems

Terminal, Bronze Bolted

By ANDERSON
Catalog # [V453](#)



Bronze Bolted Cable Terminal Adapter Transformer Terminal to Multiple Cables; Bronze terminal adapter for connecting two, three, or four copper cables to NEMA secondary transformer terminals. Material: Castings-Bronze alloy, Eyebolt-High strength bronze, Hardware-silicon bronze or stainless steel".

Features

- High strength bronze eyebolts and bronze alloy casting terminal adapter
- two, three, or four copper cables to NEMA secondary transformer terminals

General

EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Silicon Bronze
Number of Eyebolts	4
Number of Ground Braid Lug	0
Holes	
Type	Terminal, Adapter
UPC	096359333968

Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	2.156 lb

Electrical Ratings

Maximum Current Rating Amps 0
Continuous

Conductor Related

Conductor Diameter - Maximum	0.681 in
Conductor Diameter - Minimum	0.255 in
Conductor Diameter Range	0.255 - 0.681
Conductor Type	Copper

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)
[Sales Drawings - C-1494 \(V Product Family\)](#)
[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products](#)
[Video - Hubbell Power Systems Quick Ship](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-V453-SPEC-EN | REV 6/2024