

Terminal, Compression

By ANDERSON
Catalog # [VACL100012BN](#)



VERSAtile Aluminum Compression Terminal, 1000 MCM AL, 2 H, 1/2"

*Representative Image

Features

Rated at 34.5 KV. UL listed for aluminum or copper conductors. CSA certified.

General

Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
Die Size	*See Resources / Downloads for die selection and installation instructions
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy - Tin Plated
Material - Body	Aluminum
Number of Pad Holes	2
Physical Attribute - Number of Holes	2
Style	Pressed Tubing
UPC	096359333999

Dimensions

Diameter - Pad Bolt	0.5 in
Dimension - Bolt Hole Size inch	0.500 in
Weight	1.372 lb

Conductor Related

Conductor Compatibility	ACSR-Egret-636-30/19;ACSR-Flamingo-666.6-24/7;ACSR-Gannet-666.6-26/7;ACSR-Stilt-715.5-24/7;ACSR-Starling-715.5-26/7;ACSR-Redwing-715.5-30/19;ACSR-Coot-795-36/1;ACSR-Cuckoo-795-24/7;ACSR-Drake-795-26/7;ACSR-Tern-795-45/7;ACSR-Condor-795-54/7;ACSR-Mallard-795-30/19;ACSR-Ruddy-900-45/7;AAC-Cattail-750-61;AAC-Arbutus-795-37;AAC-Lilac-795-61;AAC-Cockscomb-900-37;AAC-Snapdragon-900-61;AAC-Magnolia-954-37;AAC-Goldenrod-954-61;AAC-Camellia-1000-61;ACAR-853.7-30/7
Conductor Diameter (VersaCrimp) - Maximum	1.152 in
Conductor Diameter (VersaCrimp) - Minimum	0.998 in

Certifications And Compliance

UL Listed	Yes
-----------	-----

Logistics

Carton Quantity	12
Pallet Quantity	960

Product Assets

[Catalogs - Distribution Connectors](#)
[Installation Manuals - VACL Terminal Die Chart](#)
[Sales Drawings - VACL Terminal Sales Drawing](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-VACL100012BN-SPEC-EN | REV 6/2024