

Terminal, Compression

By ANDERSON
Catalog # [VACL1516](#)



VERSAtile Aluminum Compression Terminal

*Representative Image

Features

- Rated at 34.5 KV. UL listed for aluminum or copper conductors. CSA certified.

General

Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
Die Size	*See Resources / Downloads for die selection and installation instructions
Material	Aluminum Alloy - Tin Plated
Material - Body	Aluminum
Number of Pad Holes	1
Physical Attribute - Number of Holes	1
Style	Pressed Tubing
UPC	096359355403

Dimensions

Diameter - Pad Bolt	0.31 in
Dimension - Bolt Hole Size inch	0.310 in
Weight	0.098 lb

Conductor Related

Conductor Compatibility	ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18
Conductor Diameter (VersaCrimp) - Maximum	0.332 in
Conductor Diameter (VersaCrimp) - Minimum	0.232 in

Certifications and Compliance

UL Listed	Yes
-----------	-----

Logistics

Carton Quantity	250
-----------------	-----

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Installation Manuals - VACL Terminal Die Chart](#)
[Sales Drawings - VACL Terminal Sales Drawing](#)