

VERSAtile Aluminum Compression Terminal 300 MCM AL/CU; 3/8" pad bolt diameter; single hole

By ANDERSON
Catalog # [VCEL03038H1](#)



VERSAtile Aluminum Compression Terminal 300 MCM AL/CU; 3/8" pad bolt diameter; single hole

Features

- CSA certified, UL Listed for both concentric and compact aluminum and concentric copper conductor

General

Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy - Tin Plated
Material - Body	Aluminum
Number of Pad Holes	1
Number of Spade Holes	1
Plating Type	Tin
Style	Impact Extruded
UPC	096359336464

Dimensions

Bolt Diameter	0.38
Diameter - Pad Bolt	0.38 in
Weight	0.098 lb

Conductor Related

Conductor Compatibility	ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;ACSR-Pigeon-3/0-6/1;ACSR-Penguin-4/0-6/1;ACSR-Waxwing-266.8-18/1;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18;AAAC 6201 Alloy-Anaheim-155.4-6/18;AAAC 6201 Alloy-Amherst-195.7-6/18;AAAC 6201 Alloy-Alliance-246.9-6/18
-------------------------	--

Conductor Diameter (Die Type Tooling) - Maximum 0.63 in

Conductor Diameter (Die Type Tooling) - Minimum 0.629 in

Conductor Diameter (VersaCrimp) - Maximum 0.63 in

Conductor Diameter (VersaCrimp) - Minimum 0.232 in

Lug Conductor Type

- AL
- CU

Certifications and Compliance

UL Listed Yes

Logistics

Carton Quantity 12
Pallet Quantity 4800

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Installation Manuals - VCEL installation instructions](#)
[Sales Drawings - VCEL_drawing](#)
[Sales Drawings - CC-11191](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
AN-VCELO3038H1-SPEC-EN | REV 1/2024