

VERSAtile Aluminum Compression  
Terminal 350 MCM AL/CU; 3/8" pad  
bolt diameter; single hole



By ANDERSON  
Catalog # [VCEL03538H1](#)

VERSAtile Aluminum Compression Terminal 350 MCM AL/CU;  
3/8" pad bolt diameter; single hole

Features

CSA certified, UL Listed for both concentric and compact  
aluminum and concentric copper conductor

General

Catalog Number	VCEL03538H1
Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy - Tin Plated
Material - Body	Aluminum
Number of Pad Holes	1
Number of Spade Holes	1
Plating Type	Tin
Style	Impact Extruded
UPC	096359336488

Dimensions

Bolt Diameter	0.38
Diameter - Pad Bolt	0.38 in
Weight	0.098 lb

Conductor Related

Conductor Compatibility	ACSR-Waxwing-266.8- 18/1;ACSR-Partridge-266.8- 26/7;ACSR-Ostrich-300-
-------------------------	-----------------------------------------------------------------------------

26/7;AAC-Valerian-250-  
19;AAC-Laurel-266.8-19;AAC-  
Tulip-336.1-19;AAC-Daffodil-  
350-19

Conductor Diameter (Die Type Tooling) - Maximum	0.681 in
Conductor Diameter (Die Type Tooling) - Minimum	0.675 in
Conductor Diameter (VersaCrimp) - Maximum	0.681 in
Conductor Diameter (VersaCrimp) - Minimum	0.574 in
Lug Conductor Type	<ul style="list-style-type: none"><li>• AL</li><li>• CU</li></ul>

Certifications And Compliance

UL Listed	Yes
-----------	-----

Logistics

Carton Quantity	96
Pallet Quantity	4320

Product Assets

[Catalogs - Distribution Connectors](#)  
[Installation Manuals - VCEL Installation Instructions](#)  
[Sales Drawings - VCEL\\_drawing](#)  
[Sales Drawings - CC-11191](#)  
[Specifications - VCEL03538H1](#)