

## Terminal, Compression

By ANDERSON  
Catalog # [VACL214](#)

VERSAtile Aluminum Compression Terminal, #2 str AL/CU, 1 H, 1/4"



\*Representative Image

### Features

- Rated at 34.5 KV. UL listed for aluminum or copper conductors. CSA certified.

### General

Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
Die Size	*See Resources / Downloads for die selection and installation instructions
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy - Tin Plated
Material - Body	Aluminum
Number of Pad Holes	1
Physical Attribute - Number of Holes	1
Style	Pressed Tubing
UPC	096359334071

### Dimensions

Diameter - Pad Bolt	0.25 in
Dimension - Bolt Hole Size inch	0.250 in
Weight	0.245 lb

### Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;AAC-Peachbell-6-7;AAC-Rose-4-7;AAC-Iris-2-7;AAAC 6201 Alloy-Akron-30.58-6/18;AAAC 6201 Alloy-Alton-48.69-6/18
Conductor Diameter (VersaCrimp) - Maximum	0.292 in
Conductor Diameter (VersaCrimp) - Minimum	0.184 in

### Certifications and Compliance

UL Listed	Yes
-----------	-----

### Logistics

Carton Quantity	200
-----------------	-----

### Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)  
[Installation Manuals - VACL Terminal Die Chart](#)  
[Sales Drawings - VACL Terminal Sales Drawing](#)