

HUBBELL Power Systems

Terminal, Compression

By ANDERSON

Catalog # [VACL35012BN](#)



VERSAtile Aluminum Compression Terminal

*Representative Image

Features

Rated at 34.5 KV. UL listed for aluminum or copper conductors. CSA certified.

General

Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
Die Size	*See Resources / Downloads for die selection and installation instructions
Material	Aluminum Alloy - Tin Plated
Material - Body	Aluminum
Number of Pad Holes	2
Physical Attribute - Number of Holes	2
Style	Pressed Tubing
UPC	096359334170

Dimensions

Diameter - Pad Bolt	0.5 in
Dimension - Bolt Hole Size inch	0.500 in
Weight	0.294 lb

Conductor Related

Conductor Compatibility	ACSR-Quail-2/0-6/1;ACSR-Pigeon-3/0-6/1;ACSR-Penguin-4/0-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAC-Oxlip-4/0-7;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Tulip-336.1-19;AAC-Daffodil-350-19;AAAC 6201 Alloy-Anaheim-155.4-6/18;AAAC 6201 Alloy-Amherst-195.7-6/18;AAAC 6201 Alloy-Alliance-246.9-6/18
Conductor Diameter (VersaCrimp) - Maximum	0.681 in
Conductor Diameter (VersaCrimp) - Minimum	0.414 in

Certifications And Compliance

UL Listed	Yes
-----------	-----

Logistics

Carton Quantity	48
-----------------	----

Product Assets

[Catalogs - Distribution Connectors](#)
[Installation Manuals - VACL Terminal Die Chart](#)
[Sales Drawings - VACL Terminal Sales Drawing](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-VACL35012BN-SPEC-EN | REV 6/2024