

VERSAtile Copper Compression
Terminal lug 750 MCM CU; 1/2" pad
bolt diameter; single hole

By ANDERSON
Catalog # [VCELC07512H1](#)



VERSAtile Copper Compression Terminal lug 750 MCM CU; 1/2"
pad bolt diameter; single hole

*Representative Image

Features

-
-
-

General

Catalog Number	VCELC07512H1
Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
Inhibitor Loaded	No
Material	Copper
Material - Body	Copper Rod
Number of Pad Holes	1
Number of Spade Holes	1
Physical Attribute - Number of Holes	1
Plating Type	Tin
Style	Impact Extruded
UPC	096359336617

Dimensions

Bolt Diameter	0.5
Diameter - Pad Bolt	0.5 in
Dimensions	3.650 in x 1.300 in x 0.50 in
Height	0.5 in
Length	3.65 in

Length Before Compression	0 in
Weight	0.703 lb
Width	1.3 in

Conductor Related

Conductor Diameter (Die Type Tooling) - Maximum	0.998 in
Conductor Diameter (Die Type Tooling) - Minimum	0.998 in
Conductor Diameter (VersaCrimp) - Maximum	0.813 in
Conductor Diameter (VersaCrimp) - Minimum	0.726 in
Lug Conductor Type	CU

Certifications And Compliance

UL Listed	Yes
-----------	-----

Logistics

Carton Quantity	36
-----------------	----

Product Assets

- [Catalogs - Distribution Connectors](#)
- [Sales Drawings - VCELC_drawing](#)
- [Sales Drawings - CC-11191](#)
- [Specifications - VCELC07512H1](#)