


Compression Splice VERSAtile™ Minimum Tension

By ANDERSON
Catalog # VANS11



Partial Tension versatile Compression Splice for #2 - #1 str
AL/CU, #2 ACSR

*Representative Image

Features

- For use with either VersaCrimp or conventional tooling.

General

Color Code	Red
Compression Method	VersaCrimp or Conventional Die Tooling
Die Size	*See Resources / Downloads for die selection and installation instructions
Material	Aluminum Alloy
UPC	096359334576

Dimensions

Length	4.25 in
Weight	0.098 lb

Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;AAC-Peachbell-6-7;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAAC 6201 Alloy-Akron-30.58-6/18;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18
Conductor Diameter (VersaCrimp) - Maximum	0.332 in
Conductor Diameter (VersaCrimp) - Minimum	0.128 in

Certifications and Compliance

UL Listed	No
-----------	----

Logistics

Pallet Quantity	9600
-----------------	------

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Installation Manuals - VANS Compression Splice Installation](#)
[Sales Drawings - VANSxx_drawing](#)