

Y-Clevis Eye, Rotated

By ANDERSON
Catalog # [YCS1059013](#)

Y-clevis eyes are primarily used to attach clamping devices to yoke plates or other associated hardware in a bundle conductor assembly. The bent bolt in the Y-section provides an additional point of articulation within an assembly. Material: body - galvanized steel, hardware - galvanized steel.



*Representative Image

Features

Bent bolt in Y-section provides an additional port of articulation within an assembly, Material: Body-Galvanized Ductile Iron, Hardware-Galvanized Steel, Cotter Pin-Stainless Steel

General

Catalog Number	YCS1059013
Material	Ductile Iron
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	YCS-90 Series
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate Body	0 lb
UPC	096359344605

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Eye Hole	0.813 in
Diameter - Pin	0 in
Dimensions	1.063 in x 2.438 in x 0.688 in
Height	0.688 in
Insulator Throat Diameter - Maximum	0 in

Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length	1.063 in
Length - Coupling	2.438 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	2.366 lb
Width	2.438 in
Width - Eye	1.063 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Logistics

Pallet Quantity	720
-----------------	-----

Product Assets

- [Catalogs - Transmission Connectors Catalog - Full](#)
- [Sales Drawings - YCS1059013 CUTSHEET](#)
- [Specifications - YCS1059013](#)