

HUBBELL

Power Systems

Aluminum Compression Terminal for 700 - 800 AL, 636 24/7, 26/7, 666.6 24/7, 715.5 36/1 ACSR, 900 COMPACT

By ANDERSON
 Catalog # [VAUL80012BN](#)

Aluminum Compression Terminal for 700 - 800 AL, 636 24/7, 26/7, 666.6 24/7, 715.5 36/1 ACSR, 900 COMPACT



*Representative Image

Features

Connectors are prefilled with rubber compatible inhibitor and sealed with color coded end caps.

General

Catalog Number	VAUL80012BN
Color Code	None
Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
Die Size	*See Resources / Downloads for die selection and installation instructions
Material	Aluminum
Material - Body	Aluminum
Number of Pad Holes	2
Physical Attribute - Number of Holes	2
Plating	No
Style	Impact Extruded
UPC	096359334996

Dimensions

Diameter - Pad Bolt	0.5 in
Dimension - Hole Size inch	0.500 in
Dimensions	7.250 in x 1.600 in x 0.630 in
Height	0.63 in
Length	7.25 in
Weight	0.796 lb
Width	1.6 in

Conductor Related

Conductor Compatibility	ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Parakeet-556.5-24/7;ACSR-Dove-556.5-26/7;ACSR-Eagle-556.5-30/7;ACSR-Peacock-605-24/7;ACSR-Squab-605-26/7;ACSR-Teal-605-30/19;ACSR-Kingbird-636-18/1;ACSR-Swift-636-36/1;ACSR-Rook-636-24/7;ACSR-Grosbeak-636-26/7;ACSR-Egret-636-30/19;ACSR-Flamingo-666.6-24/7;ACSR-Gannet-666.6-26/7;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37;AAC-Orchid-636-37;AAC-Flag-700-61;AAC-Violet-715.5-37;AAC-Nasturtium-715.5-61;AAC-Cattail-750-61;AAC-Arbutus-795-37;AAC-Lilac-795-61;AAC-Snapdragon-900-61;ACAR-653.1-12/7;ACAR-739.8-18/19
Conductor Diameter (VersaCrimp) - Maximum	1.031 in
Conductor Diameter (VersaCrimp) - Minimum	0.806 in

Certifications And Compliance

UL Listed	No
-----------	----

Logistics

Carton Quantity 40

Product Assets

[Catalogs - Distribution Connectors](#)

[Installation Manuals - VAUL Terminals Installation Procedures](#)

[Sales Drawings - VAULxxx_drawing](#)

