

Aluminum Suspension Bundling Yoke

By ANDERSON
Catalog # [YPW1513912](#)



Type YPW yokes are used to vertically bundle conductors on new or rebuilt lines. Consequently, information as to conductor sizes, types of armor rod, if used, conductor spacing, ultimate strengths and existing clamp details must be given at time of ordering. YPW yokes are designed for use with Anderson™ clamps. Because YPW yokes may be furnished in a variety of sizes, conductor spacing, and ultimate strengths for both low voltage and EHV application, please contact factory for more details. Material: Yoke Plate-Aluminum Alloy, Clevis Bolt & Nut-Galvanized steel, Cotter Pin-Stainless Steel; Supplied with Clevis Bolt, Cotter Pin and Nut.

Features

Vertically bundle conductors on new or rebuilt lines, designed for use with Anderson clamps

General

EU RoHS Indicator	No
Material	Aluminum
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	YPW Series
Strength Rating - Ultimate	15000 lb
Strength Rating - Ultimate	0 lb
Body	
Type	Suspension Tangent Yokes
UPC	096359471042

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length - Coupling	12 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	1.96 lb

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Logistics

Pallet Quantity	540
-----------------	-----

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-YPW1513912-SPEC-EN | REV 6/2024