


HUBBELL Power Systems

Compression Splice VERSAtile™ Minimum Tension

By ANDERSON
Catalog # [VAUS108](#)



Aluminum, Minimum tension, Reducing splice for 1/0 TO #8

*Representative Image

Features

- See product drawing for complete reducing range
- Entire VAUS series installs with only 4 common die sizes
- Color coded end caps for quick conductor sizing through 4/0

General

Catalog Number	VAUS108
Color Code	Yellow; Green
Compression Method	VersaCrimp or Conventional Die Tooling
Cover Available	No
Die Size	*See Resources / Downloads for die selection and installation instructions
EU RoHS Indicator	Contact Manufacturer
End A Type	1/0 str AL/CU/ACSR
End B Type	#8 str AL, #8 str - #6 sol CU
Material	Aluminum Alloy
UPC	096359356912

Dimensions

Length Before Compression	2 in
---------------------------	------

Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;AAC-Peachbell-6-7;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAAC 6201 Alloy-Akron-30.58-6/18;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18
Conductor Diameter (Conventional Tooling) End A - Maximum	0.186 in
Conductor Diameter (Conventional Tooling) End A - Minimum	0.421 in
Conductor Diameter (Conventional Tooling) End B - Maximum	0.186 in
Conductor Diameter (Conventional Tooling) End B - Minimum	0.421 in

Logistics

Carton Quantity	400
-----------------	-----

Product Assets

[Catalogs - Distribution Connectors](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-VAUS108-SPEC-EN | REV 6/2024