



* Representative image

Coupler, Aluminum Bolted

by ANDERSON
Catalog ID: ASTC207

Coupler, Straight, Tube to Cable, Aluminum Bolted, 2 IPS/EHIPS tube to 0.563 - 0.744 cable. COUPLER, AL 2.0 IPS TO .563-.744 IN

- Hex Stops on the casting allows for one-wrench installation

Product Details

General

Bolt Installation Torque (Recommended)	300 in-lbs
Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Type	Tube to Cable Couplers
UPC	096359285571

Dimensions

Base Hole Spacing	0 in
Diameter - Clamping Hardware	0.5 in
Diameter - Rod / Tube	2 in
Weight	1.470 lb

Electrical Ratings

Maximum Current Rating Amps Continuous	See Technical Advisor
----------------------------------------	-----------------------

Conductor Related

Conductor Compatibility	ACSR-Penguin-4/0-6/1;ACSR-Waxwing-266.8-18/1;ACSR-Partridge-266.8-26/7;ACSR-Ostrich-300-26/7;ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brahma-203.2-16/19;AAC-Valerian-250-19;AAC-Laurel-266.8-19;AAC-Tulip-336.1-19;AAC-Daffodil-350-19;AAC-Canna-397.5-19
Conductor Diameter (Tap) - Maximum	0.744 in
Conductor Diameter (Tap) - Minimum	0.563 in
Conductor Type	Aluminum Bus

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com