


Compression Splice VERSAtile™ Minimum Tension

By ANDERSON
Catalog # VAUS3030



Aluminum, Minimum tension, Reducing splice for 3/0 CU, AAC, ACSR.

*Representative Image

Features

- See product drawing for complete reducing range
- Entire VAUS series installs with only 4 common die sizes
- Color coded end caps for quick conductor sizing through 4/0

General

Color Code	Black
Compression Method	VersaCrimp or Conventional Die Tooling
Cover Available	No
Die Size	*See Resources / Downloads for die selection and installation instructions
EU RoHS Indicator	Contact Manufacturer
End A Type	3/0 str AL/CU/ACSR - 4/0 COMP
End B Type	3/0 str AL/CU/ACSR - 4/0 COMP
Material	Aluminum Alloy
UPC	096359335207

Dimensions

Diameter - Outside	0.906 in
Weight	0.196 lb

Conductor Related

Conductor Compatibility	ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;ACSR-Quail-2/0-6/1;ACSR-Pigeon-3/0-6/1;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAC-Phlox-3/0-7;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18;AAAC 6201 Alloy-Azusa-123.3-6/18;AAAC 6201 Alloy-Anaheim-155.4-6/18
Conductor Diameter (Conventional Tooling) End A - Maximum	0.502 in
Conductor Diameter (Conventional Tooling) End A - Minimum	0.464 in
Conductor Diameter (Conventional Tooling) End B - Maximum	0.502 in
Conductor Diameter (Conventional Tooling) End B - Minimum	0.464 in
Conductor Diameter (VersaCrimp Tooling) End A - Maximum	0.502 in
Conductor Diameter (VersaCrimp Tooling) End A - Minimum	0.232 in
Conductor Diameter (VersaCrimp Tooling) End B - Maximum	0.502 in
Conductor Diameter (VersaCrimp Tooling) End B - Minimum	0.232 in

Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)
[Sales Drawings - CC-11615](#)

