



* Representative image

Coupler, Aluminum Bolted

by ANDERSON
Catalog ID: ASTC409

Coupler, Straight, Tube to Cable, Aluminum Bolted, 4 IPS/EHIPS tube to 0.681 - 0.893 cable. COUPLER, AL 4.0 IPS TO .681-893 IN

- Hex Stops on the casting allows for one-wrench installation

Product Details

General

Bolt Installation Torque (Recommended)	300 in-lbs
Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Type	Tube to Cable Couplers
UPC	096359348016

Dimensions

Base Hole Spacing	0 in
Diameter - Clamping Hardware	0.5 in
Diameter - Rod / Tube	4 in
Weight	3.626 lb

Electrical Ratings

Maximum Current Rating Amps Continuous	See Technical Advisor
--	-----------------------

Conductor Related

Conductor Compatibility	ACSR-Merlin-336.4-18/1;ACSR-Linnet-336.4-26/7;ACSR-Oriole-336.4-30/7;ACSR-Chickadee-397.5-18/1;ACSR-Brant-397.5-24/7;ACSR-Ibis-397.5-26/7;ACSR-Lark-397.5-30/7;ACSR-Pelican-477-18/1;ACSR-Flicker-477-24/7;ACSR-Hawk-477-26/7;ACSR-Hen-477-30/7;ACSR-Osprey-556.5-18/1;ACSR-Brahma-203.2-16/19;AAC-Canna-397.5-19;AAC-Cosmos-477-19;AAC-Syringa-477-37;AAC-Zinnia-500-19;AAC-Hyacinth-500-37;AAC-Dahlia-556.5-19;AAC-Mistletoe-556.5-37;AAC-Meadowsweet-600-37
Conductor Diameter (Tap) - Maximum	0.893 in
Conductor Diameter (Tap) - Minimum	0.681 in
Conductor Type	Aluminum Bus

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsc@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com