



* Representative image

Tee, Aluminum Bolted

by ANDERSON
Catalog ID: ATCC1515

Tee, Aluminum Bolted, Cable to Cable, 1.289-1.459 Main to 1.081-1.293 Tap.
TEE, AL BLT 1113-1272 TO 1113-1272 ACSR

Product Details

General

Material	Aluminum
Material - Clamping Hardware	Aluminum Alloy
Number of Ground Braid Lug Holes	0
Type	Tee, Bolted
UPC	096359286813

Dimensions

Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in
Weight	2.352 lb

Electrical Ratings

Maximum Current Rating Amps Continuous	0
--	---

Conductor Related

Conductor Compatibility	ACSR-Finch-1113-54/19;ACSR-Bunting-1192.5-45/7;ACSR-Grackle-1192.5-54/19;ACSR-Bittern-1272-45/7;ACSR-Pheasant-1272-54/19;ACSR-Dipper-1351.5-45/7;ACSR-Martin-1351.5-54/19;ACSR-Bobolink-1431-45/7;AAC-Narcissus-1272-61;AAC-Columbine-1351.5-61;AAC-Carnation-1431-61;AAC-Gladiolus-1510.5-61;AAC-Coreopsis-1590-61
Conductor Diameter (Main) - Maximum	1.459 in
Conductor Diameter (Main) - Minimum	1.289 in
Conductor Diameter (Main) Range	1.289 - 1.459
Conductor Diameter (Tap) - Maximum	1.293 in
Conductor Diameter (Tap) - Minimum	1.081 in
Conductor Type	- AAC - ACSR

Logistics

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscs@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com