

HUBBELL

Power Systems

VERSAtile Aluminum Compression Terminal for 1/0 str AL/CU; 3/8" pad bolt diameter; single hole

By ANDERSON
Catalog # [VCEL02138H1](#)



VERSAtile Aluminum Compression Terminal for 1/0 str AL/CU; 3/8" pad bolt diameter; single hole

Features

CSA certified, UL Listed for both concentric and compact aluminum and concentric copper conductor

General

Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy - Tin Plated
Material - Body	Aluminum
Number of Pad Holes	1
Number of Spade Holes	1
Plating Type	Tin
Style	Impact Extruded
UPC	096359336419

Dimensions

Bolt Diameter	0.38
Diameter - Pad Bolt	0.38 in
Weight	0.029 lb

Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;AAC-Peachbell-6-7;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAAC 6201 Alloy-Akron-30.58-6/18;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18
Conductor Diameter (Die Type Tooling) - Maximum	0.373 in
Conductor Diameter (Die Type Tooling) - Minimum	0.368 in
Conductor Diameter (VersaCrimp) - Maximum	0.373 in
Conductor Diameter (VersaCrimp) - Minimum	0.146 in
Lug Conductor Type	AL CU

Certifications And Compliance

UL Listed	Yes
-----------	-----

Product Assets

[Catalogs - Distribution Connectors](#)
[Installation Manuals - VCEL installation instructions](#)
[Sales Drawings - VCEL_drawing](#)
[Sales Drawings - CC-11191](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-VCELO2138H1-SPEC-EN | REV 6/2024