

# HUBBELL

## Power Systems

### VERSAtile Aluminum Compression Terminal for 1/0 str AL/CU; 5/16" pad bolt diameter; single hole

By ANDERSON

Catalog # [VCEL021516H1](#)



VERSAtile Aluminum Compression Terminal for 1/0 str AL/CU; 5/16" pad bolt diameter; single hole

#### Features

CSA certified, UL Listed for both concentric and compact aluminum and concentric copper conductor

#### General

Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy - Tin Plated
Material - Body	Aluminum
Number of Pad Holes	1
Number of Spade Holes	1
Physical Attribute - Number of Holes	
Plating Type	Tin
Style	Impact Extruded
UPC	096359336426

#### Dimensions

Bolt Diameter	0.31
Diameter - Pad Bolt	0.31 in
Dimension - Bolt Hole Size inch	
Length Before Compression	
Weight	0.029 lb

#### Conductor Related

Conductor Compatibility	ACSR-Turkey-6-6/1;ACSR-Swan-4-6/1;ACSR-Swanate-4-7/1;ACSR-Sparrow-2-6/1;ACSR-Sparate-2-7/1;ACSR-Robin-1-6/1;AAC-Peachbell-6-7;AAC-Rose-4-7;AAC-Iris-2-7;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAAC 6201 Alloy-Akron-30.58-6/18;AAAC 6201 Alloy-Alton-48.69-6/18;AAAC 6201 Alloy-Ames-77.47-6/18
Conductor Diameter (Die Type Tooling) - Maximum	0.373 in
Conductor Diameter (Die Type Tooling) - Minimum	0.368 in
Conductor Diameter (VersaCrimp) - Maximum	0.373 in
Conductor Diameter (VersaCrimp) - Minimum	0.146 in
Lug Conductor Type	AL CU

#### Certifications And Compliance

UL Listed	Yes
-----------	-----

#### Logistics

Carton Quantity	100
Pallet Quantity	32000

#### Product Assets

- [Catalogs - Distribution Connectors](#)
- [Installation Manuals - VCEL installation instructions](#)
- [Sales Drawings - VCEL\\_drawing](#)
- [Sales Drawings - CC-11191](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
AN-VCLE021516H1-SPEC-EN | REV 6/2024