



Tee, Aluminum Bolted

by ANDERSON
Catalog ID: ATCF16301

Tee, Aluminum Bolted, Cable to Flat, 1289-1459 Main to 3 in, 4 hole Flat Tap. TEE, AL BOLT, 1.382-1.632 IN, C PAD



* Representative image

Product Details

General

| | |
|----------------------------------|----------------|
| Material | Aluminum |
| Material - Clamping Hardware | Aluminum Alloy |
| Number of Ground Braid Lug Holes | 0 |
| Number of Pad Holes | 4 |
| Type | Tee, Bolted |
| UPC | 096359287117 |

Dimensions

| | |
|---------------------------|----------|
| Base Hole Spacing | 0 in |
| Diameter - Base Holes | 0 in |
| Diameter - Bolt | 0 in |
| Diameter - Inside | 0 in |
| Length - Coupling | 0 in |
| Length Before Compression | 0 in |
| Weight | 3.626 lb |
| Width - Flat Bar Tap | 3 in |

Electrical Ratings

| | |
|--|---|
| Maximum Current Rating Amps Continuous | 0 |
|--|---|

Conductor Related

| | |
|-------------------------------------|--|
| Conductor Compatibility | ACSR-Pheasant-1272-54/19;ACSR-Dipper-1351.5-45/7;ACSR-Martin-1351.5-54/19;ACSR-Bobolink-1431-45/7;ACSR-Plover-1431-54/19;ACSR-Nuthatch-1510.5-45/7;ACSR-Parrot-1510.5-54/19;ACSR-Lapwing-1590-45/7;ACSR-Falcon-1590-54/19;ACSR-Chukar-1780-84/19;AAC-Gladiolus-1510.5-61;AAC-Coreopsis-1590-61;AAC-Cowslip-2000-91 |
| Conductor Diameter (Main) - Maximum | 1.459 in |

| | |
|-------------------------------------|--|
| Conductor Diameter (Main) - Minimum | 1.289 in |
| Conductor Diameter (Main) Range | 1.289 - 1.459 |
| Conductor Type | <ul style="list-style-type: none">• AAC• ACSR |

For further technical assistance, please contact us

Domestic Customer Service

Hubbell Power Systems
210 N. Allen Centralia, MO 65240 USA
Phone: (573) 682-5521
Fax: (573) 682-8475
Email: hpscsh@hubbell.com

International Customer Service

Phone: +1-573-682-5521
Fax: +1-573-682-8516
Email: hpsintlcs@hubbell.com