

## VERSAtile Aluminum Compression Terminal 2/0 str AL/CU; 5/16" pad bolt diameter; single hole

By ANDERSON  
Catalog # [VCEL022516H1](#)



VERSAtile Aluminum Compression Terminal 2/0 str AL/CU;  
5/16" pad bolt diameter; single hole

### Features

- CSA certified, UL Listed for both concentric and compact aluminum and concentric copper conductor

### General

Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Alloy - Tin Plated
Material - Body	Aluminum
Number of Pad Holes	1
Number of Spade Holes	1
Plating Type	Tin
Style	Impact Extruded
UPC	096359336433

### Dimensions

Bolt Diameter	0.31
Diameter - Pad Bolt	0.31 in
Weight	0.098 lb

### Conductor Related

Conductor Compatibility	ACSR-Robin-1-6/1;ACSR-Raven-1/0-6/1;AAC-Pansy-1-7;AAC-Poppy-1/0-7;AAC-Aster-2/0-7;AAAC 6201 Alloy-Azusa-123.3-6/18
Conductor Diameter (Die Type Tooling) - Maximum	0.419 in
Conductor Diameter (Die Type Tooling) - Minimum	0.414 in
Conductor Diameter (VersaCrimp) - Maximum	0.419 in
Conductor Diameter (VersaCrimp) - Minimum	0.328 in
Lug Conductor Type	<ul style="list-style-type: none"> <li>• AL</li> <li>• CU</li> </ul>

### Certifications and Compliance

UL Listed	Yes
-----------	-----

### Logistics

Carton Quantity	12
Pallet Quantity	7680

### Product Assets

[Catalogs - Distribution Connectors \(CA05127E\)](#)  
[Installation Manuals - VCEL installation instructions](#)  
[Sales Drawings - VCEL\\_drawing](#)  
[Sales Drawings - CC-11191](#)