



# 2.4/5/6 GHZ 6 DBI 6 ELEMENT INDOOR/OUTDOOR TRI-BAND PATCH ANTENNA WITH RPSMA ATS-03287 (ATS-OP-2456-6-6RPSP-36)



# **ELECTRICAL SPECIFICATIONS**

Frequency Range: 2.4-2.48/5.15-5.85/6-7.125 GHz

Gain: 6 dBi

Polarization: Vertical

Horizontal Beamwidth: 70°/70°/70° Vertical Beamwidth: 70°/70°/70° VSWR:  $\leq$ 1.5:1, max 2.0 Isolation: >30 dB Impedance: 50  $\Omega$ 

Lightning Protection: None Max Input Power: 50 W per port





# **MECHANICAL SPECIFICATIONS**

Dimensions: 11.81"x 11.81"x 2.36"

(300x300x60mm) Weight: 1.5 lb (0.68 kg)

Installation: Flush Mount to Wall

Radome Material: ABS Connector: RPSMA Number of Leads: 6 Cable Length: 36" (910mm) Cable Type: ATS-200



# **ENVIRONMENTAL SPECIFICATIONS**

Installation Environment: Indoor/Outdoor

Operating Temperature: -40 to 158°F (-40 to 70°C)

Wind Velocity: 134 mph (216 km/h)

### **WARRANTY**

2 Year Limited Warranty



# **HORIZONTAL**

# 114.00 11

### **VERTICAL**

