

VERSAtile Copper Compression  
Terminal lug 300 MCM CU; 3/8" pad  
bolt diameter; single hole

By ANDERSON  
Catalog # [VCELC03038H1](#)



VERSAtile Copper Compression Terminal lug 300 MCM CU- 3/8"  
pad bolt diameter- single hole

\*Representative Image

Features

- For use with stranded copper conductor only
- Compact design for use in molded case equipment where space is limited
- Color coded bands or easy die selection. CSA certified, UL Listed

General

Catalog Number	VCELC03038H1
Crimp Method	VERSAtile™ (Accommodates Conventional And Anderson Tools)
EU RoHS Indicator	Contact Manufacturer
Inhibitor Loaded	No
Material	Copper
Material - Body	Copper Rod
Number of Pad Holes	1
Number of Spade Holes	1
Physical Attribute - Number of Holes	1
Plating Type	Tin
Style	Impact Extruded
UPC	096359336587

Dimensions

Bolt Diameter	0.38
Diameter - Pad Bolt	0.38 in
Dimensions	2.260 in x 1.000 in x 0.281 in

Height	0.281 in
Length	2.26 in
Length Before Compression	0 in
Weight	0.293 lb
Width	1 in

Conductor Related

Conductor Diameter (Die Type Tooling) - Maximum	0.63 in
Conductor Diameter (Die Type Tooling) - Minimum	0.629 in
Conductor Diameter (VersaCrimp) - Maximum	0.373 in
Conductor Diameter (VersaCrimp) - Minimum	0.414 in
Lug Conductor Type	CU

Certifications And Compliance

UL Listed	Yes
-----------	-----

Logistics

Pallet Quantity	7680
-----------------	------

Product Assets

[Catalogs - Distribution Connectors](#)  
[Sales Drawings - VCELC\\_drawing](#)  
[Sales Drawings - CC-11191](#)  
[Specifications - VCELC03038H1](#)