


Terminal, Bronze Bolted

By ANDERSON
Catalog # [VL3D92DHSF](#)

"Terminal, Bronze Bolted, Cable to Flat, Eyebolt style, Cable Dia. Range 0.162"-0.575" to 1-5/8" Flat Pad with 2 Holes, Material: Castings-Bronze alloy, Eyebolt-High strength bronze, Hardware-silicon bronze or stainless steel"



*Representative Image

Features

- "Double eyebolt provides high pullout resistance
- Cable entrance only from end of terminal
- 90° Pad orientation available, 45° Pad orientation available
- Side formed tongue will be supplied when a center formed tongue is standard"

General

EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Eyebolts	3
Number of Pad Holes	4
Type	Bolted Lugs & Terminals
UPC	096359339380

Dimensions

Angle - Pad	180 °
Weight	13.720 lb
Width - Pad	4 in

Conductor Related

Conductor Diameter - Maximum	1.412 in
Conductor Diameter - Minimum	1.152 in
Conductor Diameter Range	1.152 - 1.412
Conductor Type	Copper

Product Assets

[Catalogs - Substation Connectors \(SA\)](#)
[Sales Drawings - C-4818-1 \(VL Product Family\)](#)
[Sales Drawings - C-4818-2 \(VL Product Family\)](#)
[Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products \(VI05050E0619\)](#)
[Video - Hubbell Power Systems Quick Ship \(VI05124E1018\)](#)