



2.4/5 GHz 13 dBi 4 Element Indoor/Outdoor Patch Antenna with DART

By AccelTex Solutions
Catalog # [ATS-01085](#)

ATS-01085 (former catalog number ATS-OP-245-13-1DART-36). AccelTex Solutions 4 Element Dual Band Wi-Fi Indoor/Outdoor Patch Antenna with DART connector is a perfect compliment to any enterprise-class AP to achieve directional coverage in your indoor or outdoor space.

Features

- 4-element dual band patch antenna with DART connector
- Designed for directional Wi-Fi coverage in indoor and outdoor spaces

General

| | |
|------------------------|---|
| Antenna Gain | 13 dBi |
| Antenna Type | Patch |
| Beamwidth - Horizontal | 15° |
| Beamwidth - Vertical | 120° |
| Cable Type | RG402 Plen |
| Catalog Number | ATS-01085 |
| Compatibility | <ul style="list-style-type: none">• Cisco Catalyst 9120AXE• Cisco Catalyst 9120AXP |
| Connector Type | DART |
| Indoor/Outdoor | Indoor or Outdoor |
| Input Power - Max | 50 W per port |
| Installation Type | Flush Mount to Wall or Articulating Wall/Pole Mount |
| Isolation Loss | >30 dB |
| Material - Radome | ABS |



| | |
|-----------------------|-----------------------------|
| Number of Leads | 4 |
| Operating Temperature | -40 to 70 °C |
| Polarization | Horizontal |
| Technology | 802.11ac, 802.11ax, 802.11n |
| UPC | 662620435831 |
| Windage | 134 mph (216 km/h) |

Dimensions

| | |
|------------|----------------------------|
| Dimensions | 13.8 in x 13.8 in x 1.4 in |
| Height | 1.4 in |
| Length | 13.8 in |
| Width | 13.8 in |

Electrical Ratings

| | |
|------------------|-------------------------|
| Frequency Rating | 2.4-2.485/5.15-5.85 GHz |
| Impedance | 50 Ohms |
| Voltage Ratio | < 1.5:1, Max 2.0 |

Product Assets

[Specifications - Specification Sheet](#)



A Hubbell brand