


Terminal, Bronze Bolted

By ANDERSON

Catalog # [VL44D89DH](#)



Bronze alloy terminal, with double eyebolt clamping for connecting four copper cables to copper flat. Double eyebolt provides high pullout resistance. Tongue holes have NEMA spacing. 45 deg and 90 deg angle connectors may be obtained by specifying desired angle at the end of catalog number. Material: Castings-Bronze alloy, Eyebolt-High strength bronze, Hardware-silicon bronze or stainless steel.

Features

- "Double eyebolt provides high pullout resistance
- Cable entrance only from end of terminal
- 90° pad orientation available, 45° pad orientation available"

General

Catalog Number	VL44D89DH
EU RoHS Indicator	No
Material	Bronze
Material - Clamping Hardware	Stainless Steel
Number of Eyebolts	4
Number of Ground Braid Lug Holes	0
Number of Pad Holes	4
Type	Terminal / Lug, Bolted
UPC	096359339434

Dimensions

Angle - Pad	180 °
Base Hole Spacing	0 in
Diameter - Base Holes	0 in
Diameter - Bolt	0 in
Diameter - Inside	0 in
Length - Coupling	0 in
Length Before Compression	0 in

Weight	11.368 lb
Width - Pad	4 in

Electrical Ratings

Maximum Current Rating Amps Continuous	0
--	---

Conductor Related

Conductor Diameter - Maximum	1.152 in
Conductor Diameter - Minimum	0.365 in
Conductor Diameter Range	0.365 - 1.152
Conductor Type	Copper

Certifications And Compliance

Buy American Compliant	Contact Manufacturer
------------------------	----------------------

Product Assets

- [Catalogs - Substation Connectors \(SA\)](#)
- [Sales Drawings - C-4818-2 \(VL Product Family\)](#)
- [Sales Drawings - C-4818-1 \(VL Product Family\)](#)
- [Specifications - VL44D89DH](#)
- [Video - Hubbell Power Systems 3D Portal to help with developing 3D models of substation connector products](#)
- [Video - Hubbell Power Systems Quick Ship](#)