

HUBBELL Power Systems

Y-Clevis Ball

By ANDERSON
Catalog # [YBC30](#)

Ball Y-clevises are used to attach ball and socket insulators to other associated hardware. The bent bolt in the Y-clevis section provides an additional point of articulation. Material: Body-Galvanized Steel, Bent Bolt & Nut-Galvanized Steel, Cotter Pin-Stainless Steel; For use with ANSI class 52-3 & 52-5 insulators.



*Representative Image

Features

- Attach ball and socket insulators to other associated hardware
- For use with ANSI class 52-3 & 52-5 insulators

General

Material	Steel
Material - Pin (Clevis)	Galvanized Steel
Material - Pin (Cotter)	Stainless Steel
Number of Bolt Holes	0
Series	YBC Series
Strength Rating - Ultimate	30000 lb
Strength Rating - Ultimate	0 lb
Body	
UPC	096359344407

Dimensions

Assembly Rating (Ultimate)	0 lb
Diameter - Bolt	0 in
Diameter - Pin	0 in
Insulator Throat Diameter - Maximum	0 in
Insulator Throat Diameter - Minimum	0 in
Insulator Throat Diameter Range	0 - 0
Length	1.75 in
Length - Coupling	3.094 in
Length - Pin	0 in
Maximum Adjustment	0 in
Ring Height	0 in
Weight	1.744 lb
Width	1.5 in

Conductor Related

Conductor Diameter - Maximum	0 in
Conductor Spacing	0 in

Logistics

Pallet Quantity 1200

Product Assets

[Catalogs - Transmission Connectors Catalog - Full](#)
[Sales Drawings - YBC30 CUTSHEET](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
AN-YBC30-SPEC-EN | REV 6/2024