

195 SERIES LOW LOSS COAXIAL CABLE

ATS-195-PA#6090



> CONSTRUCTION SPECIFICATIONS

Inner Conductor

Conductor Dia. Min.Break Strength

Insulation

Insulation Dia. Color Centricity Adhesion

Shielding Foil overlap

Outer Conductor

Coverage. Braid Dia

Jacket Outer Dia Color

BC **0.94** +/-0.02mm 293 N

Solid P.E. 2.79 +/-0.10mm

10 to 100N @ 25mm

AL/P-Foil (Bonded)

≥120 %

TC Wire Braid 90 +/-3mm 3.35 +/0-15mm

3000-5800 MHz

4.95 +/-0.15mm Black

> MECHANICAL SPECIFICATIONS

Min.Bending Radius:

Installation 15 mm Repeated 50 mm 245 Max.Pulling Tension Crush resistance of cable (load of 700n) <1%

Rated Temperature

Storage/operating temperature -40~+85 °C -70~+85 °C Outdoor Installation

> ELECTRICAL SPECIFICATIONS

Characteristic Impedance	50 ±2 ohm	Attenuation (at 20 °C)		
		[MHz]	[Power kw]	[dB/100ft]
Capacitance	83 pF/m	30 MHz	0.89	1.98
Velocity ratio	80 %	50 MHz	0.68	2.56
DCR: Inner Conductor	<26 ohm/km	150 MHz	0.39	4.45
DCR: Outer Conductor	<18 ohm/km	220 MHz	0.32	5.40
Voltage withstand	4000 V RMS	450 MHz	0.22	7.77
Jacket Spark	1500 V RMS	900 MHz	0.16	11.11
•		1500 MHz	0.12	14.55
Insulation resistance	> 10,000 MΩ·km	1800 MHz	0.11	15.99
Peak Power	2.5 kw	2000 MHz	0.10	16.86
Shielding Effectiveness	> 90 dB	2500 MHz	0.09	19.00
		5800 MHz	0.06	28.89
VSWR	100-3000 MHz <1.15			

<1.25



100 SERIES LOW LOSS COAXIAL CABLE

ATS-100A-PA#6009

