



ELECTRICAL SPECIFICATIONS

Frequency Range: 698-960 / 1710-2700 MHz Gain: 2 dBi Polarization: Vertical Horizontal Beamwidth: 360° Vertical Beamwidth: 90°

VSWR: <2.5 Impedance: 50 O Max Input Power: 20 W



MECHANICAL SPECIFICATIONS

Dimensions: 8.58"x 1.02"x 0.53" {218x26x13.5mm) Weight: 1.23 oz {35 g) Installation: Direct Connect Color: White **Connector: SMA Plug** Articulation: 90°



ENVIRONMENTAL SPECIFICATIONS

WARRANTY


2 Year Limited Warranty

Installation Environment: Indoor/Outdoor

IP Rating: IP66

HORIZONTAL

VERTICAL



The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. All AccelTex Solutions products are sold pursuant to the AccelTex Solutions Terms and Conditions of Sale. © 2022 AccelTex Solutions. All Rights Reserved. AccelTex, AccelTex Solutions, the AccelTex Solutions Logo and other marks are trademarks or registered trademarks of AccelTex Solutions. Other products or service names may be the property of third parties.

1.888.406.8906 SALES@ACCELTEX.COM

-28⁻³²-40

-20

-136 132

.8 -124 -120 -116 -1'

-108

-104

-100

-96 -92

-88

-84

-80

-76


-68

60

-52 -48



698-960/1710-2700 MHZ 2 DBI LTE OMNI ANTENNA WITH SMA PLUG CONNECTOR ATS-ID90RD-LTE-2-1SP-IC-W



The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. All AccelTex Solutions products are sold pursuant to the AccelTex Solutions Terms and Conditions of Sale. © 2022 AccelTex Solutions. All Rights Reserved. AccelTex, AccelTex Solutions, the AccelTex Solutions Logo and other marks are trademarks or registered trademarks of AccelTex Solutions. Other products or service names may be the property of third parties.

1.888.406.8906 SALES@ACCELTEX.COM