AccelTex s o L U T I O N S

GPS/LTE/WIFI 7 ELEMENT INDOOR/OUTDOOR OMNI ANTENNA WITH SMA AND RPSMA ATS-00-7IN1-2832-3SP-4RPSP-18

ELECTRICAL SPECIFICATIONS

GPS & GLONASS Antenna

Frequency Range: 1575.42-1610 MHz Gain: 28 dB Polarization: Right Hand Circular Noise Figure: <1.5 dB

LTE Antenna Frequency Range: 698-960/1710-2690 MHz Gain: 3 dBi Polarization: Linear

Wi-Fi Antenna Frequency Range: 2.4-2.483/4.9-5.825 GHz Gain: 2 dBi Polarization: Linear



MECHANICAL SPECIFICATIONS

Dimensions: 4.33" Dia x 2.09" H (110mm Dia x 53mm H) Weight: 1.25 lb (0.57 kg) Installation: Threaded Bolt with Nut Cable Type: RG174



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Outdoor Operating Temperature: -40 to 185°F (-40 to 85°C) IP Rating: IP66 VSWR: ≤2.0 Impedance: 50 Ω Supply Voltage: 3-5V DC Current Consumption: < 15 mA

VSWR: ≤3.0 Impedance: 50 Ω



VSWR: ≤2.5 Impedance: 50 Ω

> Radome Material: ABS Connector: 3 SMA (1 GPS & 2 LTE) 4 RPSMA (Wi-Fi) Number of Leads: 7 Cable Length: 18" (457.2mm)

WARRANTY

2 Year Limited Warranty

The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. All AccelTex Solutions products are sold pursuant to the AccelTex Solutions Terms and Conditions of Sale. © 2022 AccelTex Solutions. All Rights Reserved. AccelTex, AccelTex Solutions, the AccelTex Solutions Logo and other marks are trademarks or registered trademarks of AccelTex Solutions. Other products or service names may be the property of third parties.

1.888.406.8906 SALES@ACCELTEX.COM