



# GPS/LTE/CBRS/WiFi 9 Element Indoor/Outdoor Omni Antenna with SMA and RPSMA

By AccelTex Solutions  
Catalog # [ATS-01082](#)

ATS-01082 (former catalog number ATS-OO-9in1-2832-5SP-4RPSP-18). The AccelTex Solutions 9 in 1 GPS/LTE/Wi-Fi antenna is a perfect compliment to any multi-band radio. This small form factor antenna comes with an integrated threaded bolt mount and is suitable for a broad range of outdoor applications.

### Features

- 9-in-1 GPS/LTE/Wi-Fi antenna with integrated threaded bolt mount
- Designed for multi-band radios in outdoor environments

### Application

High Density, Indoor Wi-Fi, Outdoor Wi-Fi, Stadium

### General

Antenna Gain	GPS: 25 dBi / LTE: 3 dBi / WiFi: 2 dBi
Antenna Type	Omni
Beamwidth - Horizontal	360°
Beamwidth - Vertical	90°/70°/90°
Cable Type	RG174
Catalog Number	ATS-01082
Compatibility	<ul style="list-style-type: none"><li>•</li><li>•</li></ul>
Connector Type	4 RPSMA Plug, 5 SMA
Indoor/Outdoor	Outdoor



Installation Type	Threaded Bolt with Nut
Number of Leads	9
Operating Temperature	-40 to 85 °C
Polarization	GPS: Right Hand Circular / LTE: Linear / WiFi: Linear
Technology	802.11ac, 802.11n
UPC	662620435800

### Dimensions

Height	2.6 in
Length	5.1 in
Width	0 in

### Electrical Ratings

Frequency Rating	698-960/1575.42-1610/1710-2690/3300-3800/2400-2483
Impedance	50 Ohms
Voltage Ratio	< 2.0-3.0

### Product Assets

[Specifications - Specification Sheet](#)



A Hubbell brand