

2.4/5 GHZ 8 DBI 4 ELEMENT INDOOR/OUTDOOR PATCH ANTENNA WITH RPSMA ATS-OP-245-8-4RPSP-36



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.5 / 5.1-5.85 GHz

Gain: 8 dBi

Polarization: 2 Vertical, 2 Horizontal Horizontal Beamwidth: 125° / 114° Vertical Beamwidth: 35° / 24° VSWR: <1.5:1 Max: 2.0

Isolation: >20dB Impedance: 50 Ω





MECHANICAL SPECIFICATIONS

Dimensions: 12.6"x 6.7"x 1.4"(320mm x 170mm x 35mm)

Radome Material: ABS Connector: RPSMA Plug Number of Leads: 4 Cable Length: 36" (910mm) Cable Type: ATS-195



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor

IP Rating: IP66


WARRANTY


2 Year Limited Warranty



2.4GHZ


5GHZ









2.4/5 GHZ 8 DBI 4 ELEMENT INDOOR/OUTDOOR PATCH ANTENNA WITH RPSMA ATS-OP-245-8-4RPSP-36










2.4/5 GHZ 8 DBI 4 ELEMENT INDOOR/OUTDOOR PATCH ANTENNA WITH RPSMA ATS-OP-245-8-4RPSP-36

Threaded Inserts:



*NOTE: The threaded inserts labeled "B" in the above graphic are 1/4"-20TPI and are meant to be used with I-beam clamps for easy mounting to the I-beams