



## 2.4/5 GHz 7 dBi 6 Element Indoor/Outdoor Patch Antenna with RPSMA

By AccelTex Solutions  
Catalog # [ATS-01113](#)

ATS-01113 (former catalog number ATS-OP-245-7-6RPSP-36). The AccelTex Solutions dual band indoor/outdoor 6-Element patch antenna is a perfect complement to any enterprise-class AP to achieve directional coverage in your indoor or outdoor space. Each antenna element is optimized for Wi-Fi operation on both 2.4 and 5 GHz. This antenna comes with integrated mounting holes in the corners of the radome and leads exiting the bottom of the antenna for a flush wall mount. This highly versatile antenna is suitable for a broad range of indoor and outdoor applications where focused RF coverage of an area is desired.

### Features

- 6-element dual band patch antenna optimized for 2.4 and 5 GHz Wi-Fi
- Integrated mounting holes for flush wall installation

### Application

Indoor Wi-Fi, Outdoor Wi-Fi

### General

Antenna Gain	7/6 dBi
Antenna Type	Patch
Beamwidth - Horizontal	100°/110°
Beamwidth - Vertical	59°/61°
Cable Type	ATS-200
Catalog Number	ATS-01113
Compatibility	<ul style="list-style-type: none"><li>• Arista C-230E</li><li>• Aruba/HP AP-518</li><li>• Mist AP43e</li></ul>
Connector Type	RPSMA Plug
Indoor/Outdoor	Indoor or Outdoor
Installation Type	Flush Mount to Wall or Articulating Mount (included)
Material - Radome	ABS



Number of Leads	6
Operating Temperature	-40 to 70 °C
Polarization	3 Vertical, 3 Horizontal
Technology	802.11ac, 802.11ax, 802.11n
UPC	662620436050
Windage	134 mph (216 km/h)

### Dimensions

Dimensions	12.6 in x 6.7 in x 1.4 in
Height	1.4 in
Length	12.6 in
Width	6.7 in

### Electrical Ratings

Frequency Rating	2.4-2.485/5.15-5.85 GHz
------------------	-------------------------

### Logistics

Carton Quantity	5
Pallet Quantity	60

### Product Assets

[Specifications - Specification Sheet](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved  
ATS-ATS01113-SPEC-EN | REV 4/2025