



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.48/5.15-5.85/6-7.125 GHz
 Gain: 7/7/7 dBi
 Polarization: 5 Vertical / 5 Horizontal
 Horizontal Beamwidth: 120°/105°/105°
 Vertical Beamwidth: 75°/60°/60°
 VSWR: <2.0



MECHANICAL SPECIFICATIONS

Dimensions: 11.8" x 11.8" x 1.85" (300x300x47mm)
 Weight: 1.5 lb (0.68 kg)
 Installation: Flush Mount to Wall or
 Articulating wall/pole mount (included)

Radome Material: ABS
 Connector: 4MPC & 6MPC
 Number of Leads: 10
 Cable Length: 36" (910mm)
 Cable Type: RG316



ENVIRONMENTAL SPECIFICATIONS


Installation Environment: Due to LPI requirements, Indoor only
 IP Rating: IP66

WARRANTY

2 Year Limited Warranty



HORIZONTAL



VERTICAL

