



2.4/5 GHz 8 dBi 6 Element Indoor/Outdoor Patch Antenna with N-Style

By AccelTex Solutions
Catalog # [ATS-01126](#)

ATS-01126 (former catalog number ATS-OP-245-8-6NP-36). The AccelTex Solutions dual band indoor/outdoor patch antenna is a perfect complement to any enterprise-class AP to achieve directional coverage in your indoor or outdoor space. Each antenna element is optimized for Wi-Fi operation on both 2.4 and 5 GHz. This antenna comes with integrated mounting holes in the corners of the radome and leads exiting the bottom of the antenna for a flush wall mount. This highly versatile antenna is suitable for a broad range of indoor and outdoor applications where focused RF coverage of an area is desired. We call this one our "Half Warehouse" antenna.

Features

- Dual band patch antenna optimized for 2.4 and 5 GHz Wi-Fi
- Includes integrated mounting holes for flush wall installation
- Ideal for "Half Warehouse" coverage

Application

Indoor Wi-Fi, Outdoor Wi-Fi

General

Antenna Gain	8 dBi
Antenna Type	Patch
Beamwidth - Horizontal	100°/100°
Beamwidth - Vertical	40°/25°
Cable Type	ATS-195
Catalog Number	ATS-01126
Compatibility	<ul style="list-style-type: none">• Arista O-235E• Aruba/HP AP-574• Cisco Catalyst 9124AXE• Mist AP63E
Connector Type	N-Style Plug
Indoor/Outdoor	Indoor or Outdoor



Installation Type	Wall Mount or Articulating Mount
Material - Radome	ABS
Number of Leads	6
Operating Temperature	-40 to 65 °C
Polarization	3 Vertical, 3 Horizontal
Technology	802.11ac, 802.11ax, 802.11n
UPC	662620436166
Windage	134 mph (216 km/h)

Dimensions

Dimensions	12.6 in x 10.3 in x 1.4 in
Height	1.4 in
Length	12.6 in
Width	10.3 in

Electrical Ratings

Frequency Rating	2.4-2.5/4.9-5.85 GHz
Impedance	50 Ohms

Product Assets

[Specifications - Specification Sheet](#)



A Hubbell brand

©2025 Hubbell Incorporated. All rights reserved
ATS-ATS01126-SPEC-EN | REV 4/2025