



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.48/5.15-5.85/6-7.125 GHz
 Gain: 6/6/6 dBi
 Polarization: Vertical
 Horizontal Beamwidth: 105°/105°/105°
 Vertical Beamwidth: 85°/60°/50°

VSWR: ≤1.5:1, max 2.0
 Isolation: >30 dB
 Impedance: 50 Ω
 Lightning Protection: None
 Max Input Power: 50 W per port



MECHANICAL SPECIFICATIONS

Dimensions: 15.4" x 15.4" x 2.16" (390x390x55mm)
 Weight: 6.61 lb (3 kg)
 Installation: Flush Mount to Wall

Radome Material: ABS
 Connector: Right-Angle DART
 Number of Leads: 1 (8 ports on DART Assembly)
 Cable Length: 36" (910mm)
 Cable Type: ATS-100



ENVIRONMENTAL SPECIFICATIONS


Installation Environment: Indoor/Outdoor
 Operating Temperature: -40 to 158°F (-40 to 70°C)
 Wind Velocity: 134 mph (216 km/h)
 IP Rating: IP66

WARRANTY

2 Year Limited Warranty



HORIZONTAL



VERTICAL

