



Ethernet Surge Suppressor 10GB for 802.3at, 802.3af and 802.3bt

By AccelTex Solutions
Catalog # [ATS-01693](#)



Bi-directional Ethernet Surge Suppressor 10GB, Lightning and Surge Protection

Features

- Integrated mounting feet and a DIN rail clip for easy installation
- Equipped with RJ-45 connectors for straightforward integration into existing networks
- Designed for both standalone and DIN rail mounting for versatile installation options
- High-speed data compatibility without compromising performance

Application

Indoor Wi-Fi, Outdoor Wi-Fi

General

Catalog Number	ATS-01693
Connector Type	RJ-45 Jack
Data Transfer Rate	1/10 Gbps
Forms	Test Value
Humidity	0-95% non-condensing
Installation Type	Integrated Mounting Feet and DIN Rail Clip

Insulation R-Value	Greater than 10,000 megaohms
Material - Housing	Cast Aluminum
Operating Temperature	-40 to 85 °C
Storage Temperature Range	'-40 to 194 F (-40 to 90 C)
Technology	802.11ax, 802.3af, 802.3at
UPC	662620436999

Dimensions

Dimensions	5.25 in x 1.75 in x 2.25 in
Height	2.25 in
Length	5.25 in
Width	1.75 in

Electrical Ratings

Maximum Clamping Voltage	24-650V, 64-650V, PoE 6V-18.3V
Operating Voltage	Data 56 to 58V, PoE 58 V

Product Assets

[Installation Manuals - Ethernet Surge Suppressor Installation Guide](#)
[Specifications - Specification Sheet](#)



A Hubbell brand