



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.48/5.15-5.85/6-7.125 GHz
Gain: 8/8/8 dBi
Polarization: 4 Vertical, 4 Horizontal
Horizontal Beamwidth: 115°/110°/110°
Vertical Beamwidth: 50°/25°/25°

VSWR: <2.5
Isolation: >30 dB
Impedance: 50 Ω
Lightning Protection: None
Max Input Power: 50 W per port



MECHANICAL SPECIFICATIONS

Dimensions: 12.99"x12.99"x1.37"
(330x330x35mm)
Weight: 2.5 lb (0.68 kg)
Installation: Flush Mount or Articulating Mount
(included)

Radome Material: ABS
Connector: N-Style
Number of Leads: 8
Cable Length: 36" (910mm)
Cable Type: ATS-195



ENVIRONMENTAL SPECIFICATIONS


Installation Environment: Indoor/Outdoor
Operating Temperature: -40 to 158°F (-40 to 70°C)
Wind Velocity: 134 mph (216 km/h)
IP Rating: IP66

WARRANTY

2 Year Limited Warranty



HORIZONTAL



VERTICAL

