

2.4/5 GHZ 4/2 DBI 6 ELEMENT INDOOR/OUTDOOR 90°/90° HD PATCH ANTENNA WITH RPSMA ATS-OHDP-245-42-6RPSP-36



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.5/4.9-5.85 GHz Gain: 4 / 2 dBi Polarization: 3 Horizontal—3 Vertical Horizontal Beamwidth: 80°/90° Vertical Beamwidth: 80°/90° VSWR: < 2.0:1 Isolation: >20 dB Impedance: 50 Ω Lightning Protection: DC Grounded Max Input Power: 100 W per port





MECHANICAL SPECIFICATIONS

Dimensions: 8.1"x 7"x 1.8" (205.7x178x45.7mm) Weight: 1.2 lb (0.54 kg) Installation: Threaded Bolt w/ Nut or Articulating Wall/Pole Mount (included) Installation Hole Diameter: 1" (25.4mm) Pole Mount Diameter: 2" (50.8mm)



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor Operating Temperature: -40 to 149°F (-40 to 65°C) Wind Velocity: 130 mph (209 km/h) IP Rating: IP66 Radome Material: ASA Connector: RPSMA Number of Leads: 6 Cable Length: 36" (914.4 mm) Cable Type: ATS-195


WARRANTY

2 Year Limited Warranty



HORIZONTAL

VERTICAL



The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. ©2023 AccelTex Solutions. All Rights Reserved.

1.888.406.8906 SALES@ACCELTEX.COM