

2.4/5/6 GHZ 12 DBI 8 ELEMENT INDOOR/OUTDOOR HIGH DENSITY PATCH ANTENNA WITH RIGHT ANGLE DART ATS-OHDP-2456-131212-8PRADART-ND-36



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.48/5.15-5.85/6-7.125 GHz

Gain: 12/12/12 dBi

Polarization: Vertical and Horizontal Horizontal Beamwidth: 35°/30°/30° Vertical Beamwidth: 35°/30°/30°

VSWR: <2



MECHANICAL SPECIFICATIONS

Dimensions: 19.3"x 19.3"x 2.44"(490x490x62mm)

Weight: 2.2 lb (4 kg)

Installation: Flush Mount to Wall or Articulation Mount

Radome Material: ASA

Connector: Right-Angle DART-8

Number of Leads: 1 (8 ports on DART Assembly)

Cable Length: 36" (910mm) Cable Type: ATS-100



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor

IP Rating: IP66


WARRANTY

2 Year Limited Warranty



HORIZONTAL

VERTICAL





2.4/5/6 GHZ 12 DBI 8 ELEMENT INDOOR/OUTDOOR HIGH DENSITY PATCH ANTENNA WITH RIGHT ANGLE DART ATS-OHDP-2456-131212-8PRADART-ND-36

