

2.4/5/6 GHZ 8 DBI 8 ELEMENT INDOOR/OUTDOOR PATCH ANTENNA WTH 8 PORT RIGHT ANGLE DART ATS-OP-2456-8-8PRADART-ND-36



### **ELECTRICAL SPECIFICATIONS**

Frequency Range: 2.4-2.48/5.15-5.85/6-7.125 GHz Gain: 8/8/8 Polarization: 4 Vertical, 4 Horizontal Horizontal Beamwidth: 115°/110°/110° Vertical Beamwidth: 50°/25°/25° VSWR: <2.5 Isolation: >30 dB Impedance: 50 Ω Lightning Protection: None Max Input Power: 50 W per port





## **MECHANICAL SPECIFICATIONS**

Dimensions: 12.99"x 12.99"x 1.37" (330x330x35mm) Weight: 2.5 lb (1 kg) Installation: Flush Mount to Wall/Ceiling or Articulation Arm

Radome Material: ABS Connector: Right Angle DART-8 Number of Leads: 8 Cable Length: 36" (910mm) Cable Type: ATS-100



## **ENVIRONMENTAL SPECIFICATIONS**

Installation Environment: Indoor/Outdoor Operating Temperature: -40 to 158°F (-40 to 70°C) Wind Velocity: 134 mph (216 km/h) IP Rating: IP66


#### WARRANTY

2 Year Limited Warranty

# нс

# HORIZONTAL





The facts and figures herein are carefully compiled to the best of our knowledge and are intended for general informational purposes only. Responsibility for the use and application of AccelTex Solutions materials rests with the end user. All AccelTex Solutions products are sold pursuant to the AccelTex Solutions Terms and Conditions of Sale. © 2023 AccelTex Solutions. All Rights Reserved. AccelTex, AccelTex Solutions, the AccelTex Solutions Logo and other marks are trademarks or registered trademarks of AccelTex Solutions. Other products or service names may be the property of third parties.

1.888.406.8906 SALES@ACCELTEX.COM