

2.4/5/6 GHZ 8/10/10 DBI 8 ELEMENT TRI-BAND PATCH ANTENNA WITH RIGHT ANGLE DART ATS-OP-2456-81010-8PRADART-ND-36



ELECTRICAL SPECIFICATIONS

Frequency Range: 2.4-2.48/5.15-5.85/6-7.125 GHz

Gain: 8/10/10 dBi

Polarization: 4 Vertical / 4 Horizontal Horizontal Beamwidth: 65°/45°/40° Vertical Beamwidth: 65°/45°/40°

VSWR: ≤1.5:1, max 2.0 Isolation: >30 dB Impedance: 50 Ω

Lightning Protection: None Max Input Power: 50 W per port





MECHANICAL SPECIFICATIONS

Dimensions: 15.4"x 15.4"x 1.57"(390x390x40mm)

Weight: 1.5 lb (0.68 kg)

Articulating Mount (included)

Installation: Flush Mount to Wall or use

Radome Material: ABS

Connector: Right-Angle DART

Number of Leads: 1 (8 ports on DART Assembly)

Cable Length: 36" (910mm) Cable Type: ATS-100



ENVIRONMENTAL SPECIFICATIONS

Installation Environment: Indoor/Outdoor

Operating Temperature: -40 to 158°F (-40 to 70°C)

Wind Velocity: 134 mph (216 km/h)

IP Rating: IP66

WARRANTY

2 Year Limited Warranty



HORIZONTAL

VERTICAL

