



# Indoor/Outdoor Compression Driver - 13314 Series (16 ohm)

By Austdac  
Catalog # [13314-002](#)

A compression drivers that is designed to provide optimum performance in both commercial and industrial applications. These indoor/outdoor compression drivers are commonly used in light and heavy manufacturing facilities with high ambient noise, and corrosive and hazardous environments.

## Features

- Low Distortion, Superior Sound
- Rain-Tight, Chemical Resistant Housing
- Suitable for Harsh or Corrosive Environments
- Variable Impedance Drivers
- Fits GAI-TRONICS' Horns with 1 3/8" - 18 UNEF Threads
- NEMA 4X

## General

Catalog Number	13314-002
Operating Temperature	-40° C to +70° C (-40° F to +158° F)
UPC	850025795029

## Dimensions

Weight	3.1 lb
--------	--------



## Electrical Ratings

Impedance	16 ohm
-----------	--------

## Certifications And Compliance

Hazardous Rating(s)	<ul style="list-style-type: none"><li>• Class I, Div. 2, Groups A, B, C, D</li><li>• Class II, Div. 2, Groups F, G</li><li>• Class III, Div. 2</li></ul>
Nema Rating	4X

## Product Assets

[Installation Manuals - Model 13314-002 Div. 2 Hazardous Area 16-Ohm Horn Driver](#)  
[Installation Manuals - Speaker/Horn Installation for GAI-TRONICS Communication Systems](#)  
[Literature - Indoor / Outdoor Compression Driver](#)